

	Stock Code	Dimension	Qty	Approx. wt./lb. Each
 <p><b>PEX PRESS SLEEVES</b> These stainless steel sleeves provide a secure press fit for the Viega PEX Press system. The view hole can be used to verify full tubing insertion. Use only with Viega PEX Press fittings and tools. <b>DISCOUNT 6</b> <u>model 2811.5</u></p>		<b>PEX Press</b>		
	<b>61000</b>	3/8	100	0.006
	<b>61020</b>	1/2	100	0.007
	<b>61030</b>	5/8	100	0.008
	<b>61040</b>	3/4	100	0.01
	<b>61060</b>	1	100	0.016
	<b>61070</b>	1 1/4	50	0.041
	<b>61080</b>	1 1/2	50	0.048
 <p><b>PEX PRESS COPPER TUB ELS</b> Copper tub els allow ViegaPEX or FostaPEX runs to easily transition into tub and shower valves. <b>Sleeve NOT included</b> <b>DISCOUNT 6</b> <u>model 2820.0US</u></p>	<b>62220</b>	<b>PEX Press x Copper (Length)</b> 1/2 x 1/2 (3 x 6)	25	0.242
 <p><b>PEX PRESS COPPER STUB-OUT ELBOWS</b> Copper PEX Press stub-outs transition ViegaPEX or FostaPEX tubing to copper for termination at the wall. <b>Sleeve NOT included</b> <b>DISCOUNT 6</b> <u>model 2820.1US</u></p>	<b>62405</b>	<b>PEX Press x Copper (Length)</b> 3/8 x 1/2 (3.5 x 8)	25	0.296
	<b>62420</b>	1/2 x 1/2 (3.5 x 8)	25	0.30
	<b>62440</b>	3/4 x 3/4 (3.5 x 8)	25	0.51
 <p><b>PEX PRESS COPPER STRAIGHT STUB-OUTS</b> These copper stub-outs transition ViegaPEX or FostaPEX tubing to copper with a Bronze PEX Press fitting. <b>Sleeve NOT included</b> <b>DISCOUNT 6</b> <u>model 2820.2US</u></p>	<b>62608</b>	<b>PEX Press x Copper (Length)</b> 1/2 x 1/2 (8)	25	0.232
	<b>62615</b>	1/2 x 1/2 (15)	25	0.388
 <p><b>PEX PRESS COPPER TEE STUB-OUT</b> Copper PEX Press Stub-Out Tee transitions ViegaPEX or FostaPEX tubing to copper for termination at the wall maintaining a low profile flow through type installation. <b>Sleeve NOT included</b> <b>DISCOUNT 6</b> <u>model 2820.3US</u></p>	<b>62300</b>	<b>PEX Press x Copper (Length)</b> 1/2 x 1/2 x 1/2 (8)	25	